

**Aven Inc.**  
4595 Platt Rd.  
Ann Arbor, MI 48108  
**Phone:** 734.973.0099  
**Email:** [info@aventools.com](mailto:info@aventools.com) • **Web Address:** [www.aventools.com](http://www.aventools.com)

All Categories > Optical Inspection Tools > Stereo and Stereo Zoom Microscopes > Create Your Own Microscope System > NSW Stereo Microscope Body > Item # NSW-20

### Item # NSW-20, Dual Magnification 10x & 20x Stereo Body



[larger image](#)

- Dual Magnification 10x & 20x Stereo Body
- 10x Wide Field Eyepieces (F.N. 23)
- Field of View: 23 mm (0.91") at 10x, 11.5 mm (0.45") at 20x
- Rubber Eye Guards
- Dust Cover
- Dual Magnification of 6x & 20x, 10x & 20x, 10x & 30x and 20x & 40x bodies available

[To Configure Your System Select](#) • [Specifications](#) • [Options](#) • [Note](#)

#### To Configure Your System Select

1. The microscope body that meets your magnification, field of view and working distance requirements. Note with a combination of eyepieces and auxiliary lens you can tailor a system to meet your requirements.
2. Focusing Mount.
3. Stand (please take into account the working distance and the height of the stand).
4. Illumination - Fiber Optic, Fluorescent or LED.
5. Camera and or adapter if you are using a trinocular body.
6. Monitor if necessary.

#### Specifications

<b>Body</b>	10x & 20x Stereo Body
<b>Eyepiece</b>	10x Wide
<b>Field of View</b>	11.5 mm (0.45") at 20x 23 mm (0.91") at 10x
<b>Magnification</b>	10x & 20x
<b>Weight</b>	2 lb

#### Options

<b>Focus Mount (Required)</b>	<a href="#">SCW-PA</a> , Focus Mount
<b>Stands</b>	<a href="#">Stand PF</a> , Stand Type PF with Focus Mount and Built in Fluorescent Light <a href="#">Stand P</a> , Pole Type Stand with Focus Mount <a href="#">Stand T</a> , Stand Type T with Focus Mount <a href="#">26800B-535</a> , Standard Dual Arm Ball Bearing Boom Stand with Mounting Post <a href="#">26800B-520</a> , Boom Stand with Mounting Post <a href="#">26800B-560</a> , Articulating Arm <a href="#">26800B-570</a> , Standard Stand with Safety Clamp

<b>Illumination</b>	<a href="#">26200B-203</a> , Fluorescent Ring Light with UV Lamp <a href="#">26200B-207</a> , Fluorescent Ring Light with Focus Mount for DSZ & NSW Series <a href="#">26200A-200-10+adapter</a> , Fiber Optic Illuminator with Ringlight <a href="#">26200A-200-20</a> , Fiber Optic Illuminator w/Dbl Pipelight <a href="#">26200B-201</a> , Fluorescent Ring Light Economy, 12 watt Lamp <a href="#">26200B-202</a> , Fluorescent Ring Light Standard, 17 watt Lamp <a href="#">26200B-206</a> , Fluorescent Ring Light ESD Safe, 17 watt Lamp <a href="#">26200B-210+adapter</a> , LED Ringlight with Brightness Control <a href="#">26200B-211</a> , White LED Ring Light with Brightness & Sector Control
<b>Objective Lenses</b>	<a href="#">26800B-461</a> , Auxiliary Lens 0.5X <a href="#">26800B-462</a> , Auxiliary Lens 0.75X <a href="#">26800B-463</a> , Auxiliary Lens 1.6X <a href="#">26800B-464</a> , Auxiliary Lens 2X <a href="#">26800B-465</a> , Lens Cover
<b>Eyepieces</b>	<a href="#">26800B-444</a> , DSW-5X Eyepiece Lens <a href="#">26800B-443</a> , DSW-20X Eyepiece Lens <a href="#">26800B-452</a> , Rubber Eye Guard for DSW Eyepieces (Set of 2)
<b>Focusing Eyepieces w/ Reticle</b>	<a href="#">26800B-455</a> , 10x with 10 : 100 mm Scale <a href="#">26800B-456</a> , 10x with 5 : 100 mm Scale <a href="#">26800B-457</a> , 10x with 20 x 20 0.5 mm Squares Scale <a href="#">26800B-458</a> , 10x with 10 x 10 1 mm Squares Scale <a href="#">26800B-459</a> , 10x with 10 : 100 mm Scale with Cross Line

**Note**

0.5x Auxiliary lens cannot be used with the NSW series body with stand P. Also cannot be used with stands T and TI.

[Print](#) [Back](#)