

Aven Inc.
 4595 Platt Rd.
 Ann Arbor, MI 48108
Phone: 734.973.0099
Email: info@aventools.com • **Web Address:** www.aventools.com

All Categories > Optical Inspection Tools > Stereo and Stereo Zoom Microscopes > Create Your Own Microscope System > NSW Stereo Microscope Body > Item # NSW-620

Item # NSW-620, Dual Magnification 6x & 20x Stereo Body



[larger image](#)

- Dual Magnification 6x & 20x Stereo Body
- 10x Wide Field Eyepieces (F.N. 23)
- Field of View: 42 mm (1.82") at 6x, 11.5 mm (0.45") at 20x
- Rubber Eye Guards
- Dust Cover
- Dual Magnification of 6x & 20x, 10x & 20x, 10x & 30x and 20x & 40x bodies available

[To Configure Your System Select](#) • [Specifications](#) • [Options](#) • [Note](#)

To Configure Your System Select

1. The microscope body that meets your magnification, field of view and working distance requirements. Note with a combination of eyepieces and auxiliary lens you can tailor a system to meet your requirements.
2. Focusing Mount.
3. Stand (please take into account the working distance and the height of the stand).
4. Illumination - Fiber Optic, Fluorescent or LED.
5. Camera and or adapter if you are using a trinocular body.
6. Monitor if necessary.

Specifications

Body	60x & 20x Stereo Body
Eyepiece	10x Wide
Field of View	11.5 mm (0.45") at 20x 42 mm (1.82") at 6x
Magnification	6x & 20x
Weight	2 lb

Options

Focus Mount (Required)	SCW-PA , Focus Mount
Stands	Stand PF , Stand Type PF with Focus Mount and Built in Fluorescent Light Stand P , Pole Type Stand with Focus Mount Stand T , Stand Type T with Focus Mount 26800B-535 , Standard Dual Arm Ball Bearing Boom Stand with Mounting Post 26800B-520 , Boom Stand with Mounting Post 26800B-560 , Articulating Arm 26800B-570 , Standard Stand with Safety Clamp

Illumination	26200B-203 , Fluorescent Ring Light with UV Lamp 26200B-207 , Fluorescent Ring Light with Focus Mount for DSZ & NSW Series 26200A-200-10+adapter , Fiber Optic Illuminator with Ringlight 26200A-200-20 , Fiber Optic Illuminator w/Dbl Pipelight 26200B-201 , Fluorescent Ring Light Economy, 12 watt Lamp 26200B-202 , Fluorescent Ring Light Standard, 17 watt Lamp 26200B-206 , Fluorescent Ring Light ESD Safe, 17 watt Lamp 26200B-210+adapter , LED Ringlight with Brightness Control 26200B-211 , White LED Ring Light with Brightness & Sector Control
Objective Lenses	26800B-461 , Auxiliary Lens 0.5X 26800B-462 , Auxiliary Lens 0.75X 26800B-463 , Auxiliary Lens 1.6X 26800B-464 , Auxiliary Lens 2X 26800B-465 , Lens Cover
Eyepieces	26800B-444 , DSW-5X Eyepiece Lens 26800B-443 , DSW-20X Eyepiece Lens 26800B-452 , Rubber Eye Guard for DSW Eyepieces (Set of 2)
Focusing Eyepieces w/ Reticle	26800B-455 , 10x with 10 : 100 mm Scale 26800B-456 , 10x with 5 : 100 mm Scale 26800B-457 , 10x with 20 x 20 0.5 mm Squares Scale 26800B-458 , 10x with 10 x 10 1 mm Squares Scale 26800B-459 , 10x with 10 : 100 mm Scale with Cross Line

Note

NSW-620 will not work with Stand T.

0.5x Auxiliary lens cannot be used with the NSW series body with stand P. Also cannot be used with stands T and TI.

[Print](#) [Back](#)